Maybridge HitCreator the ultimate diversity library!

Diversity-based screening continues to be a vital tool for drug discovery. Efficiency and productivity can be improved by using screening libraries that offer maximum diversity whilst retaining drug-like properties. Faced with a bewildering array of commercially available screening libraries, each with their own differing characteristics, it can be difficult for drug discovery scientists to pick the ideal screening library for their specific requirements.

Our unique new offering takes away the need to choose between different libraries by providing exceptional coverage of drug-like chemical space with a single library. Building on more than 50 years of expertise in designing industry-leading screening libraries, the pre-plated Maybridge™ HitCreator consists of 14,000 screening compounds, derived from a rigorous analysis of more than 500,000 commercially available screening compounds. These compounds have been selected using a clustering algorithm, based on standard Daylight fingerprints and Tanimoto similarity. Each Maybridge HitCreator is conveniently supplied as dry films in Thermo Scientific™ Matrix 96 shallow-well plates or 384-well microplates.

Key features and benefits:

- High diversity applied Daylight fingerprints and Tanimoto similarity calculations based on the Tanimoto coefficient of 0.65 to produce an exceptionally diverse commercial library providing the best opportunity to find hits
- High hit probability all the compounds are drug-like, conforming to "Lipinski's Rule of Five" and additional filters, such as PSA ≤ 140Ų
- Reliability the compounds contained within the library have been screened to remove any inappropriate chemical structures, avoiding "false hits"
- Convenience all 14,000 compounds are available off the shelf, as 1 micromole in 96-well plates or 0.25 micromole in 384-well plates




Figure 1. Importance of diversity in finding hits

The figure above illustrates how a highly diverse screening library will provide a greater hit probability than larger, but less diverse libraries.






Accelerate your fragment screening program with the Maybridge Ro3 library

Fragment screening is becoming a method of choice in the quest for rapid identification of new lead molecules in drug discovery due to the higher hit probability and fewer fragments needing to be screened. The Maybridge™ Ro3 library is a proven industryleading library due to its diversity, pharmacophoric content and novelty.

Key features and benefits:

- Rule of Three (Ro3) compliance delivers superior ADME attributes
- A 30% increase in diversity over the previous library Tanimoto similarity index of 0.66 based on standard Daylight fingerprinting
- · Experimentally measured solubility guaranteed solubility of fragments in PBS buffer (1mM) ensures robust screening data and minimizes candidate attrition
- Assured quality of >95%, NMR spectrum available for each of the 2,500 compounds
- Chemically "clean" filtered to remove toxic and reactive groups

- · Chemical functionality selected to allow rapid chemical evolution and optimization of fragment hits
- · Pharmacaphore-rich, but not too complex to allow simpler interpretation of the results
- Fragment hopping is facilitated with the entire Maybridge portfolio



Discover our entire range at www.maybridge.com.

To place an order, contact your local Fisher Scientific office.



©2014 Thermo Fisher Scientific Inc. All rights reserved. All other trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries.

AMERICAS

Canada Fisher Scientific Canada www.fishersci.ca Tel: 800-234-7437 Fax: 800-463-2996

Latin America Fisher Scientific Global Export, Latin America www.fishersci.com Tel: 770-871-4725

United States Fisher HealthCare www.fisherhealthcare.com Tel: 800-640-0640 Fax: 800-290-0290

Fisher Scientific www.fishersci.com Tel: 800-766-7000 Fax: 800-926-1166

EUROPE

Austria info.austria@thermofisher.com www.at.fishersci.com Tel: 0800 20 88 40 Fax: 0800 20 66 90

Germany info.germany@thermofisher.com www.de.fishersci.com Tel: 2304 932-5 Fax: 2304 932-950

Portugal pt.fisher@thermofisher.com www.pt.fishersci.com Tel: 21 425 33 50 Fax: 21 425 33 51

Belaium

Fax: 770-871-4726

be.fisher@thermofisher.com www.be.fishersci.com Tel: 056 260 260 Fax: 056 260 270

Ireland fsie.sales@thermofisher.com

www.ie.fishersci.com Tel: 01 885 5854 Fax: 01 899 1855 Spain

es.fisher@thermofisher.com www.es.fishersci.com Tel: 902 239 303 Fax: 902 239 404

Czech Republic

info.cz@thermofisher.com www.thermofisher.cz Tel: 466 798 230 Fax: 466 435 008

Italy

it.fisher@thermofisher.com www.it.fishersci.com Tel: 02 950 59 478 Fax: 02 950 59 479

Sweden

fisher.se@thermofisher.com www.se.fishersci.com Tel: 31 352 32 00 Fax: 31 352 32 50

Denmark

kundeservice@thermofisher.com www.dk.fishersci.com Tel: 70 27 99 20 Fax: 70 27 99 29

Lithuania

sales.lt@thermofisher.com www.lt.fishersci.com Tel: +370 5 2444442 Fax: +370 5 2392756

Switzerland

info.ch@thermofisher.com www.ch.fishersci.com Tel: 056 618 41 11 Fax: 056 618 41 41

Finland

fisher.fi@thermofisher.com www.fi.fishersci.com Tel: 09-802 76 280 Fax: 09-802 76 235

The Netherlands

nl.info@thermofisher.com www.nl.fishersci.com Tel: 020 487 70 00 Fax: 020 487 70 70

United Kingdom

fsuk.sales@thermofisher.com www.fisher.co.uk Tel: 01509 555500 Fax: 01509 555111

France

fr.fisher@thermofisher.com www.fr.fishersci.com Tel: 03 88 67 14 14 Fax: 03 88 67 11 68

Norway fisher.no@thermofisher.com www.no.fishersci.com Tel: 22 95 59 59 Fax: 22 95 59 40

ASIA

India qfc.customercare@thermofisher.com www.fishersci.in Tel: +91-22-6680 3000 Fax: +91-22-6680 3001

Korea

sales.fsk@thermofisher.com www.fishersci.co.kr Tel: 02-3420-8700 Fax: 02-3420-8710

Malavsia

enquiry.my@thermofisher.com www.fishersci.com.my Tel: (603) 51228888 Fax: (603) 5121 8899

Singapore

enquiry.sg@thermofisher.com www.fishersci.com.sq Tel: (65) 6873 6006 Fax: (65) 6873 5005

OCEANIA

Australia

AUinfo@thermofisher.com www.thermofisher.com.au Fax: 1800-067-639

New Zealand

NZinfo@thermofisher.com www.thermofisher.co.nz Tel: 0800-933-966 Fax: +64 9 980 6788

