

# We Support Your Chemistry

*Your Specialized Chemical Services partner*



Reliability.  
Purity.  
Certainty.

# Specialized Chemical Services

## Meeting your bespoke research and manufacturing needs

For the times when the product you need is not readily available off the shelf from a chemical catalog, you can save time and resources by turning to the company you can trust.

Across Organics, Fisher BioReagents, Fisher Chemical and Maybridge offer one of the most comprehensive cost-effective solutions available in the market for all your production chemical needs, whether you are engaged in initial research or scaling up to full production.


We offer 50+ years of experience, a wide portfolio of products and an extensive global network of over 3,500 chemical suppliers and partner manufacturers operating under Confidentiality Disclosure Agreements.

## Manufacturing Capabilities

Our blending, distillation, crystallization, testing, packaging and filling capabilities allow us to manufacture a broad range of products and deliver tailored chemical solutions to customers in the pharmaceutical, biotech and general industrial markets.

We specialize in high-volume packaging as well as custom micro-scale weighing, while maintaining chemical purity.

CHOOSE SCS FOR YOUR MANUFACTURING AND RESEARCH NEEDS



## Contents:

Page no.

<b>Semi-Bulk &amp; Bulk Chemical Service</b>	3
<b>Choose how our products are adapted to meet your requirements</b>	4
Tailored Solvents and Solvent Blends	4
Testing Services	4
Customized Packaging and Labeling	5
Special Solutions	5
<b>High-Volume Solvent Delivery Systems</b>	6
<b>Quality &amp; Reliability</b>	7

### CHOOSE SPECIALIZED CHEMICAL SERVICES TO SUPPORT YOUR CHEMISTRY:



Manufacturing



Tailored Specifications



Mixtures and Blends



Customized Packaging



Bulk and Semi-bulk Chemicals



Research



Testing Services



Reduced waste



Sourcing Support

## Semi-Bulk & Bulk Chemical Service



The extensive catalogue offering encompasses the Acros Organics, Fisher BioReagents, Fisher Chemical and Maybridge brands. Any product from these brands is available in larger quantities to suit your semi-bulk and bulk requirements.

We can secure and manage the supply of these products using either internal manufacturing or select partners worldwide through our extensive supply-chain network.

Our sourcing team has the global reach to make the best buy available on the market without losing sight of local market demands, needs and expectations. We can provide a “lean” single supplier option and reliably manage multi-product supply projects.

Technical Sourcing specialists work with you to understand your process requirement and with our supply partners to ensure these requirements are met in full, on time.



CHOOSE SCS FOR YOUR HIGH VOLUME REQUIREMENTS AND SOURCING SUPPORT



## Choose how our products are adapted to meet



### Tailored Solvents and Solvent Blends

We can tailor make solvents to meet your specifications for your application. In addition, our dedicated solvent-mixing facilities are available to produce high-quality blends. Solvents are charged by weight, through a 0.2-micron filter, by air-driven pump and/or by nitrogen pressure. Small amounts of solid and liquid additives are added via charge-ports.

All blending and mixing operations are carried out according to written procedures. The mixing vessels are cleaned (CIP) before and after the mixing/blending operation and are left in a dry condition, filled with nitrogen, between operations.

The final product can be supplied in packaging from 1L glass bottles to stainless steel containers up to 1000L.

### Testing Services

Our extensive in-house laboratory QC capabilities\* and carefully chosen external partners allow us to respond quickly to specific quality control testing at your request on chemicals you purchase from us.

This includes method development and validation, which establishes that the performance characteristics of an analytical method are suitable for its intended purpose.

All significant method characteristics are defined:

specificity, reproducibility, accuracy, precision, linearity, limit of detection, limit of quantitation and range.

\*See page 7 for list of analytical tests and techniques we can offer.

CHOOSE SCS FOR MIXTURES, BLENDS OR TO CHANGE SPECIFICATION





## your requirements



### Customized Packaging and Labeling

Our products are available in a wide variety of innovative packaging designed for safety, environmental protection, convenient handling and storage and preservation of product integrity while complying with all relevant regulations. Custom-packing is also available for chemicals or packaging supplied by you.

Our returnable containers and FisherPaks\* are available in 10L to 1350L volumes to accommodate lab to production scale needs. By choosing this service, you will benefit from greater solvent purity and safety, improved productivity and lower environmental impact.

You also get convenience and choice with a range of accessories available to fit your laboratory needs to connect the containers to your systems, including color-coded "quick connects".\*

In addition, our custom weighing service can provide you with products from the Acros Organics and Maybridge brands at a scale from nanogram to ton – and in your own specified containers if required.

\*FisherPaks and quick connects are only available in North America.

### Special Solutions

We have experience in developing solutions for our catalog range, but if you have a special requirement for an aqueous or non-aqueous solution, we can manufacture it to your exact specifications.

CHOOSE SCS TO CHANGE PACKAGING OR LABELS



# High-Volume Solvent Delivery Systems



## Safety, efficiency and convenience

High-volume solvent delivery systems, available in 10L to 1350L, offer environmentally friendly solvent handling solutions for your applications, enhancing safety and improving productivity within your lab.

## Enhanced solvent safety

High-volume solvent delivery systems incorporate safety features to protect the lab and the environment by offering a combination of mechanical and manual controls to prevent unwanted solvent flow. The bottle-free, closed system eliminates the potential for glass bottle breakage and makes the risk of spills and exposure to vapors negligible.

## Reduce lab-operating costs

Increase lab efficiency by eliminating:

- Repeated solvent testing
- Multiple lots of material
- Bottle rinsing
- Disposal costs

## Environmentally friendly solution

- Reduce the amount of solid waste generated in your laboratory
- Minimize the release of flammable or toxic solvent liquids and vapors
- Eliminate bottle rinsing – empty containers are returned, cleaned and refilled

## For your applications

- High-performance liquid chromatography (HPLC)
- Preparative chromatography and high-volume gas chromatography sample preparation
- Process synthesis and extractions

CHOOSE SCS TO REDUCE WASTE



## Quality & Reliability



All of our manufacturing and QC processes are written in standard operating procedures and are carefully followed to assure specifications and the consistency of products we deliver.

Our manufacturing quality is reflected in a variety of certifications and licenses that we hold, including our ISO 9001:2008 and ISO 14001:2004, FDA, DEA and ATF licenses, which are regularly audited. We welcome pre-arranged customer visits to our sites to showcase our capabilities and competencies. Our testing capabilities include:

**Spectroscopy** – Atomic Absorption Spectroscopy (AAS), Inductively Coupled Plasma Mass Spectroscopy (ICP-MS), Ultraviolet-visible Spectrophotometry (UV), Fourier Transform Infrared (FTIR), Fluorescence Spectroscopy and Nuclear Magnetic Resonance (NMR).

**Chromatography** – Gas Chromatography (GC) with a range of detectors, GC-Mass Spectrometry, Ultra High Performance Liquid Chromatography (UHPLC) with diode-array or refractive index detectors, HPLC- Mass Spectrometry and Thin Layer Chromatography (TLC).

**Other capabilities** – Differential Scanning Calorimetry (DSC), optical rotation, specific gravity, density, viscosity, melting point, refractive index, Karl Fisher moisture analysis (KF), loss on drying (LOD), ash determination, particle size and color scale measurement are also available.

Specific tests can be performed on request for any of our products.

CHOOSE SCS FOR ADDITIONAL TESTING



The chemicals you need tested, packaged and delivered to your exact specification.  
Let our experts make your life easier!

To request a quotation, visit [www.wesupportyourchemistry.com](http://www.wesupportyourchemistry.com)

To place an order, contact your local Fisher Scientific office.



©2015 Thermo Fisher Scientific Inc. All rights reserved.  
All other trademarks are the property of  
Thermo Fisher Scientific Inc. and its subsidiaries.

#### EUROPE

**Austria**  
info.austria@thermofisher.com  
www.at.fishersci.com  
Tel: 0800 20 88 40  
Fax: 0800 20 66 90

**Belgium**  
be.fisher@thermofisher.com  
www.be.fishersci.com  
Tel: 056 260 260  
Fax: 056 260 270

**Czech Republic**  
info.cz@thermofisher.com  
www.thermofisher.cz  
Tel: 466 798 230  
Fax: 466 435 008

**Denmark**  
kundeservice@thermofisher.com  
www.dk.fishersci.com  
Tel: 70 27 99 20  
Fax: 70 27 99 29

**Finland**  
fisher.fi@thermofisher.com  
www.fi.fishersci.com  
Tel: 09-802 76 280  
Fax: 09-802 76 235

**France**  
fr.fisher@thermofisher.com  
www.fr.fishersci.com  
Tel: 03 88 67 14 14  
Fax: 03 88 67 11 68

**Germany**  
info.germany@thermofisher.com  
www.de.fishersci.com  
Tel: 02304 932-5  
Fax: 02304 932-950

**Ireland**  
fsie.sales@thermofisher.com  
www.ie.fishersci.com  
Tel: 01 885 5854  
Fax: 01 899 1855

**Italy**  
it.fisher@thermofisher.com  
www.it.fishersci.com  
Tel: 02 950 59 478  
Fax: 02 950 59 479

**The Netherlands**  
nl.info@thermofisher.com  
www.nl.fishersci.com  
Tel: 020 487 70 00  
Fax: 020 487 70 70

**Norway**  
fisher.no@thermofisher.com  
www.no.fishersci.com  
Tel: 22 95 59 59  
Fax: 22 95 59 40

**Portugal**  
pt.fisher@thermofisher.com  
www.pt.fishersci.com  
Tel: 21 425 33 50  
Fax: 21 425 33 51

**Spain**  
es.fisher@thermofisher.com  
www.es.fishersci.com  
Tel: 902 239 303  
Fax: 902 239 404

**Sweden**  
fisher.se@thermofisher.com  
www.se.fishersci.com  
Tel: 31 352 32 00  
Fax: 31 352 32 50

**Switzerland**  
info.ch@thermofisher.com  
www.ch.fishersci.com  
Tel: 056 618 41 11  
Fax: 056 618 41 41

**United Kingdom**  
fsuk.sales@thermofisher.com  
www.fisher.co.uk  
Tel: 01509 555500  
Fax: 01509 555111

#### ASIA

**India**  
qfc.customer@thermofisher.com  
www.fishersci.in  
Tel: +91-22-6680 3000  
Fax: +91-22-6680 3001

**Korea**  
sales.fsk@thermofisher.com  
www.fishersci.co.kr  
Tel: 02-3420-8700  
Fax: 02-3420-8710

**Malaysia**  
enquiry.my@thermofisher.com  
www.fishersci.com.my  
Tel: (603) 51228888  
Fax: (603) 5121 8899

**Singapore**  
enquiry.sg@thermofisher.com  
www.fishersci.com.sg  
Tel: (65) 6873 6006  
Fax: (65) 6873 5005

#### OCEANIA

**Australia**  
AUinfo@thermofisher.com  
www.thermofisher.com.au  
Tel: 1300-735-292  
Fax: 1800-067-639

**New Zealand**  
NZinfo@thermofisher.com  
www.thermofisher.co.nz  
Tel: 0800-933-966  
Fax: +64 9 980 6788



A Thermo Fisher Scientific Brand