

# Antiviral compounds

for research and development

Find it at [eu.fishersci.com](https://eu.fishersci.com)

# Antiviral compounds

Antiviral compounds (AVCs) are a category of antimicrobial drugs used for treating viral infections by inhibiting the development of the viral pathogen inside the host cell.

Within our Acros Organics and Alfa Aesar portfolio's we offer a broad range of high-quality compounds with known anti-viral properties in a wide range of convenient pack-sizes to facilitate your research. These products are available off-the-shelf and can be shipped very quickly to your research labs.

As an example of their application during the current Coronavirus pandemic, scientists have already identified > 70 known antiviral drugs to test against the Coronavirus.

[A New York Time article from March 23, 2020, said scientists have already identified > 70 known antiviral drugs to test against the Coronavirus.](#)


Some drugs are already used to treat other diseases, and repurposing them to treat Covid-19, the illness caused by the coronavirus, may be faster than trying to invent a new antiviral from scratch, scientists have explained.

[Browse our portfolio of antiviral products and essentials at eu.fishersci.com/go/antiviral](https://eu.fishersci.com/go/antiviral)

Fisher Scientific Cat. No.	Description	CAS Number	Size
15444939	(+)-1-Deoxynojirimycin	19130-96-2	100mg
15454939	(+)-1-Deoxynojirimycin	19130-96-2	50mg
11444563	(+)-5-Iodo-2'-deoxyuridine, 98%	54-42-2	1g
11454563	(+)-5-Iodo-2'-deoxyuridine, 98%	54-42-2	5g
10225070	(+)-5-Iodo-2'-deoxyuridine, 99%	54-42-2	1g
10649843	(+)-5-Iodo-2'-deoxyuridine, 99%	54-42-2	5g
10054043	(+)-5-Iodo-2'-deoxyuridine, 99%	54-42-2	25g
15443797	(E)-5-(2-Bromovinyl)-2'-deoxyuridine, 98%	69304-47-8	250mg
11387449	(E)-5-(2-Bromovinyl)-2'-deoxyuridine, 98%	69304-47-8	50mg
11387449	(E)-5-(2-Bromovinyl)-2'-deoxyuridine, 98%	69304-47-8	1g
15410138	1-(1-Adamantyl)ethylamine hydrochloride, 98%	1501-84-4	5g
15420138	1-(1-Adamantyl)ethylamine hydrochloride, 98%	1501-84-4	25g
11410613	1-Adamantanamine hydrochloride, 99%	665-66-7	25g
11420613	1-Adamantanamine hydrochloride, 99%	665-66-7	100g
11430613	1-Adamantanamine hydrochloride, 99%	665-66-7	500g
10645972	1-Adamantanamine hydrochloride, 99+%	665-66-7	25g
10571781	1-Adamantanamine hydrochloride, 99+%	665-66-7	100g
10142764	1-Adamantanamine, 96%	768-94-5	5g
10051694	1-Adamantanamine, 96%	768-94-5	25g
15403867	1-Adamantanamine, 98%	768-94-5	5g
15413867	1-Adamantanamine, 98%	768-94-5	25g
15423867	1-Adamantanamine, 98%	768-94-5	100g
10272262	1-Docosanol, 98%	661-19-8	25g
10581082	1-Docosanol, 98%	661-19-8	100g
13428668	2',3'-Dideoxycytidine, 98%	7481-89-2	100mg
13438668	2',3'-Dideoxycytidine, 98%	7481-89-2	500mg
11332906	2',3'-Dideoxycytidine, 98+%	7481-89-2	250mg
11322906	2',3'-Dideoxycytidine, 98+%	7481-89-2	50mg
15496599	2',3'-Dideoxyinosine, 98%	69655-05-6	1g
15406609	2',3'-Dideoxyinosine, 98%	69655-05-6	250mg
15331201	2',3'-Dideoxyinosine, 98%	69655-05-6	500mg

Fisher Scientific Cat. No.	Description	CAS Number	Size
15286058	3'-Azido-3'-deoxythymidine, 98%	30516-87-1	1g
15296058	3'-Azido-3'-deoxythymidine, 98%	30516-87-1	5g
15206068	3'-Azido-3'-deoxythymidine, 98%	30516-87-1	25g
15496739	3'-Azido-3'-deoxythymidine, 98%	30516-87-1	1g
15406749	3'-Azido-3'-deoxythymidine, 98%	30516-87-1	5g
15416749	3'-Azido-3'-deoxythymidine, 98%	30516-87-1	25g
15288155	3'-Deoxy-2',3'-didehydrothymidine, 98%	3056-17-5	1g
15246058	3'-Deoxy-2',3'-didehydrothymidine, 98%	3056-17-5	5g
15453959	5-Iodo-2'-deoxycytidine, 99%	611-53-0	1g
15463959	5-Iodo-2'-deoxycytidine, 99%	611-53-0	2g
15519463	Abacavir sulfate, 99%	188062-50-2	1g
15529463	Abacavir sulfate, 99%	188062-50-2	5g
13216319	Acycloguanosine, 98%	59277-89-3	10mg
13296309	Acycloguanosine, 98%	59277-89-3	50mg
15426229	Acycloguanosine, 98%	59277-89-3	1g
15436229	Acycloguanosine, 98%	59277-89-3	5g
15446229	Acycloguanosine, 98%	59277-89-3	25g
16651822	Adefovir dipivoxil	142340-99-6	1g
16661822	Adefovir dipivoxil	142340-99-6	10g
15678705	Atazanavir	198904-31-3	100mg
16656032	beta-Lapachone, 98%	4707-32-8	5mg
15871012	Betulinic acid	472-15-1	1g
15881012	Betulinic acid	472-15-1	250mg
16641852	Cidofovir dihydrate	149394-66-1	1g
16651852	Cidofovir dihydrate	149394-66-1	250mg
15224774	Cytarabine, 98%	147-94-4	1g
15234774	Cytarabine, 98%	147-94-4	5g
15244774	Cytarabine, 98%	147-94-4	100mg
10173294	Cytosine beta-D-arabinofuranoside hydrochloride, 99%, crystalline	69-74-9	1g
10021704	Cytosine beta-D-arabinofuranoside hydrochloride, 99%, crystalline	69-74-9	5g
15437029	Cytosine-beta-D-arabinofuranose hydrochloride	69-74-9	1g
15447029	Cytosine-beta-D-arabinofuranose hydrochloride	69-74-9	5g
15457029	Cytosine-beta-D-arabinofuranose hydrochloride	69-74-9	10g
15781789	Emtricitabine	143491-57-0	1g
15791789	Emtricitabine	143491-57-0	5g
15557719	Entecavir monohydrate, 99%	209216-23-9	1g
16661852	Famciclovir	104227-87-4	1g
16671852	Famciclovir	104227-87-4	5g
15701779	Ganciclovir, 98%	82410-32-0	1g
15711779	Ganciclovir, 98%	82410-32-0	5g
15721779	Ganciclovir, 98%	82410-32-0	25g
15406139	Imiquimod, 99%	99011-02-6	1g
15416139	Imiquimod, 99%	99011-02-6	100mg
15557049	Lamivudine, 98%	134678-17-4	1g
16504324	Limonin	1180-71-8	1g
16514324	Limonin	1180-71-8	250mg
15315088	Lopinavir, 98%	192725-17-0	1g
15325088	Lopinavir, 98%	192725-17-0	5g

Fisher Scientific Cat. No.	Description	CAS Number	Size
16544424	L-Thymidine	3424-98-4	1g
16554424	L-Thymidine	3424-98-4	5g
15507729	Nevirapine, 98%	129618-40-2	1g
15517729	Nevirapine, 98%	129618-40-2	250mg
15698715	Oseltamivir phosphate, 98%	204255-11-8	1g
15608725	Oseltamivir phosphate, 98%	204255-11-8	5g
11444030	Phosphonoacetic acid, 98+%	4408-78-0	10g
11440053	Phosphonoacetic acid, 98+%	4408-78-0	25g
11450053	Phosphonoacetic acid, 98+%	4408-78-0	100g
11450053	Raltegravir potassium salt	871038-72-1	1g
15741799	Raltegravir potassium salt	871038-72-1	250mg
15599513	Ribavirin, 98%	36791-04-5	1g
15509523	Ribavirin, 98%	36791-04-5	5g
15519523	Ribavirin, 98%	36791-04-5	25g
15547729	Ritonavir, 98%	155213-67-5	1g
15557729	Ritonavir, 98%	155213-67-5	250mg
15567729	Saquinavir mesylate, 98%	149845-06-7	100mg
11446526	Sodium phosphonoformate hexahydrate, 98+%	34156-56-4	1g
11456526	Sodium phosphonoformate hexahydrate, 98+%	34156-56-4	5g
11466526	Sodium phosphonoformate hexahydrate, 98+%	34156-56-4	25g
15811032	Sofosbuvir, 98%	1190307-88-0	250mg
16697032	Tenofovir	147127-20-6	1g
16607042	Tenofovir	147127-20-6	5g
15668725	Tenofovir disoproxil fumarate, 98%	202138-50-9	1g
15678725	Tenofovir disoproxil fumarate, 98%	202138-50-9	5g
15688725	Tenofovir disoproxil fumarate, 98%	202138-50-9	25g
15299786	Trifluorothymidine, 98%	70-00-8	1g
15255073	Trifluorothymidine, 98%	70-00-8	250mg
15733467	Valaciclovir hydrochloride hydrate	124832-27-5	5g
15743467	Valaciclovir hydrochloride hydrate	124832-27-5	25g
15618735	Valganciclovir hydrochloride, 97+%	175865-59-5	1g
16554364	Zanamivir monohydrate	1260601-68-0	1g



Contact us today:

**Austria:** +43(0)800-20 88 40 **Belgium:** +32 (0)56 260 260 **Denmark:** +45 70 27 99 20  
**Finland:** +358 (0)9 8027 6280 **France:** +33 (0)3 88 67 14 14 **Germany:** +49 (0)2304 9325  
**Ireland:** +353 (0)1 885 5854 **Italy:** +39 02 950 59 478 **Lithuania:** +370 5 2444442  
**Netherlands:** +31 (0)20 487 70 00 **Norway:** +47 22 95 59 59 **Portugal:** +351 21 425 33 50  
**Spain:** +34 902 239 303 **Sweden:** +46 31 352 32 00 **Switzerland:** +41 (0)56 618 41 11  
**UK:** +44 (0)1509 555 500

